

HUOM! ÖLJYMÄÄRÄÄ MUUTETTU ALKUPERÄISESTÄ 25,6 mL -> 24 mL



# 2022 USBC WOMEN'S CHAMPIONSHIPS



|                    |                |                 |                |
|--------------------|----------------|-----------------|----------------|
| <b>DISTANCE:</b>   | <b>42 FEET</b> | <b>VOLUME:</b>  | <b>24 mL</b>   |
| <b>RATIO:</b>      | <b>5.79:1</b>  | <b>FORWARD:</b> | <b>15,4 mL</b> |
| <b>DROP BRUSH:</b> |                | <b>REVERSE:</b> | <b>8,6 mL</b>  |
| <b>TANKS:</b>      | <b>TERRAIN</b> | <b>PUMP:</b>    | <b>50µL</b>    |



## FORWARD LOADS DATA

| # | START | STOP | LOADS | MICS | SPEED | BUFF | TANK      | DISTANCE | T.OIL |
|---|-------|------|-------|------|-------|------|-----------|----------|-------|
| 1 | 2L    | 2R   | 3     | 50   | 14    | 3    | A - Kegel | 0 → 4    | 5,550 |
| 2 | 8L    | 8R   | 2     | 50   | 18    | 3    | A - Kegel | 4 → 9    | 2,500 |
| 3 | 9L    | 9R   | 1     | 50   | 18    | 3    | A - Kegel | 9 → 11   | 1,150 |
| 4 | 10L   | 10R  | 2     | 50   | 18    | 3    | A - Kegel | 11 → 17  | 2,100 |
| 5 | 11L   | 11R  | 2     | 50   | 18    | 3    | A - Kegel | 17 → 22  | 1,900 |
| 6 | 12L   | 12R  | 2     | 50   | 18    | 3    | A - Kegel | 22 → 27  | 1,700 |
| 7 | 13L   | 13R  | 2     | 50   | 18    | 3    | A - Kegel | 27 → 32  | 1,500 |
| 8 | 2L    | 2R   | 0     | 50   | 22    | 3    | A - Kegel | 32 → 42  | 0     |



## REVERSE LOADS DATA

| # | START | STOP | LOADS | MICS | SPEED | BUFF | TANK      | DISTANCE | T.OIL |
|---|-------|------|-------|------|-------|------|-----------|----------|-------|
| 1 | 2L    | 2R   | 0     | 50   | 30    | 3    | A - Kegel | 37 → 30  | 0     |
| 2 | 12L   | 12R  | 2     | 50   | 18    | 3    | A - Kegel | 30 → 25  | 1,700 |
| 3 | 10L   | 10R  | 2     | 50   | 18    | 3    | A - Kegel | 25 → 20  | 2,100 |
| 4 | 8L    | 8R   | 1     | 50   | 18    | 3    | A - Kegel | 20 → 17  | 1,250 |
| 5 | 7L    | 7R   | 2     | 50   | 18    | 3    | A - Kegel | 17 → 12  | 2,700 |
| 6 | 6L    | 6R   | 1     | 50   | 18    | 3    | A - Kegel | 12 → 10  | 1,450 |
| 7 | 2L    | 2R   | 0     | 50   | 14    | 3    | A - Kegel | 10 → 0   | 0     |

THIS PATTERN IS DESIGNED FOR:

REVERSE DROP BRUSH

This pattern may require adjustments if using a lane machine that does not have these features



KEGEL PATTERN LIBRARY APP



PATTERNLIBRARY.KEGEL.NET



SCAN QR CODE TO  
SHARE AND  
DOWNLOAD  
THIS PATTERN

